



Collapsible spill berm ECCOTARP Collapsible spill berm CARGO



INSTRUCTIONS FOR USE US






metai arsenai°

Metal Arsenal s.r.o. Owner of Eccotarp USA trade mark ECCOTARP USA, inc. 357 West 36th Street New York, NY 10018 USA T 1 212-725-9845 Fax 212-683-8516 E info@eccofighter.com

www.eccotarp.us

This document describes the operation and characteristics of the ECCOTARP and CARGO collapsible spill berms. It contains important information about how to use the berms properly and how to increase their reliability and life. This document must always be available in the place where the berms are used. Keep it together with the berms at all times. The operator is responsible for using the berms safely and in compliance with the instructions in this manual, which applies to any third persons as well. If you have any doubts about the correct use of the berms, please contact the manufacturer or an authorized dealer.

The ECCOTARP and CARGO collapsible spill berms ("berms") are versatile protective equipment made of chemically resistant material (PVC reinforced fabric). They are **portable, lightweight and easily shapeable.** That is why they are effective especially in fast deployment during accidents. Their advantage is their adaptability to various obstacles and uneven surfaces. Due to their resistance to chemicals and petroleum products they can be used in a wide range of applications, especially in emergency services, petrochemical industry, logistic and industrial warehouses, lorry transport and shipping, during elimination of machinery defects on shop floors, at the airports and in the ports, in agriculture and forestry, i.e. everywhere where hazardous substances might leak.



Collapsible spill berm ECCOTARP

Specification of types of collapsible spill berms

Collapsible spill berms ECCOTARP

ECCOTARP collapsible spill berms have specially welded corners, which allow them to be very quickly put into the ready-for-use position. In the the upper part of the sides there are two riveted stainless-steel rings into which TPU handling belts with safety fastening hooks can be snapped. These belts can be used to move the berm easily. The berms have rigid reinforcements in the side walls.

The ECCOTARP collapsible spill berms are produced in different types and sizes so that they can be used in the widest possible range of applications – from catching minor leaks to efficient decontamination of both persons and objects.

The XL LOW is suitable for improvised decontamination of persons because it is lower than the XL HIGH berm.

The **EASY PACK** has more segmented reinforcement parts in its sides, which means it can be more easily shaped around an obstacle and folded into a smaller pack.

The **SHALLOW**'s advantage is that it can be used in badly accessible low or narrow areas. It can also be used for catching drops during the tapping and pouring of liquids.


Collapsible spill berms CARGO

Collapsible spill berms CARGO do not have welded corners, so they can be conveniently arranged around a pallet and then lifted by a fork lift or pallet truck ("sandwich": pallet, berm, pallet inside). The berms have light-weight reinforcements in the side walls.

CARGO EUR berms have perfect dimensions for being arranged around EUR-pallet. Their volume is 210 litres and they can be delivered without side handles (CARGO EUR) or with side handles (CARGO EUR Plus).

CARGO DP berms have a square shape. Their volume is 300 litres and they can be delivered without side handles (CARGO DP) or with side handles (CARGO DP Plus).


S
ē
Ð
σ
8
Ŭ
• —
2
_
υ
ă
F
4



Collapsible spill berms ECCOTARP








River and Revealed and Revea
<u>(1</u>

Type	ET 01 S	ET 02 M	ET 03L	ET 04 XL HIGH	ET 041 XLLOW	ET 051 XXI EA SV BACK	ET 06 SHALLOW
Dimensions/basin (in)	14 × 28 × 5	$28 \times 28 \times 7$	39×39×8	59 × 59 × 17	59 × 59 × 9	79 × 79 × 17	49×33×3
Capacity (gal)	7	20	46	238	119	423	13
Dimensions/unfolded (in)	37 × 14	41 × 28	55 × 39	96 × 59	77 × 59	112 × 79	54×33
Pack Size (in)	22 × 12 × 5	22 × 12 × 5	30 × 15 × 5	$47 \times 22 \times 4$	39 × 22 × 4	$40 \times 29 \times 5$	18×18×3
Weight (lb)	4	7	12	39	22	51	6
Standard accessories							
Bag (in)	10 × 21	14 × 23	20×32	24 × 50	24×41	32×41	14×18
Optional accessories at extra cost							
Pad (in)	39 × 20	51×51	51×51	87 × 87	87×87	87×87	51×51
Protective insert ET 11-16	yes	yes	yes	yes	yes	yes	
Drain hole D25/other		yes	yes	yes	yes	yes	
Ball valve D25/other		yes	yes	yes	yes	yes	
16ft hose with outlet D25		yes	yes	yes	yes	yes	


ails
Ť
a B
_
Β
Ŭ.
Ē
<u>_</u>
8
Ĕ





Type

	ET 061 CARGO EUR	
ARGO		



₽.
Δ
0
G
~
◄
U
2
9
0
L.

Dimensions (basin) (in)	49 × 33 × 9	49 × 49 × 9
Capacity (gal)	56	29
Dimensions (unfolded) (in)	67 × 51	67 × 67
Pack Size (in)	28 × 18 × 3	33.5 × 18.5 × 3
Weight (lb)	10	15
Standard accesories		
Bag ET 07 (in)	30×22	35 × 22
Optional accessories at extra cost		
Protective pad ET 09 (in)	51×51	51×51
Drain hole D25/other	yes	yes
Ball valve D25/other	yes	yes
16ft hose with outlet D25	yes	yes

General information



When using the berms, observe these instructions as well as all the safety notices herein.


- The berms are designed as fast solution for emergency situations. They are intended for catching hazardous substances leaking into the environment.
- 2. They are produced in different dimensions and versions.
- 3. Their structure can be shaped and adapted to uneven surface and other obstacles.
- 4. The berms are self-supporting.
- They are made of a chemically resistant material PVC with a protective proofing layer (PES/PVC 1.5 lb/10.7 ft²) – see Chemical resistance certificate, p. 10.
- 6. The berms are not intended for long-term storage of aggressive substances.

- 7. The range of temperatures for the use of the berms is from -22 $^\circ F$ to +158 $^\circ F.$
- 8. Their maximum carrying capacity is 441 lb.
- 9. They can be used with or without handling belts.
- 10. As a standard, the berms are delivered in transport bags.
- In order to increase the life of the berms we recommend using the following optional accessories: protective pads and protective inserts, see p. 8.
- 12. The berm can be fitted with a drain hole and a ball valve on request.


Instructions for putting the berm into the ready-to-use position

Take the berm out of the transport bag. Unfold it so that it is flat. Lift the sides and secure the corners with the yellow hooks to simply make a berm.

Illustrated instructions for unfolding the Collapsible spill berm ECCOTARP



Illustrated instructions for unfolding the Collapsible spill berm CARGO



Handling instructions and safety warnings

- 1. Put the berm onto a flat surface, if possible.
- 2. Make sure there are no sharp objects under the berm, such as pieces of broken glass, nails, sharp stones, etc., which might mechanically damage its bottom.
- 3. Do not put the product near fire or any other sources of heat.
- 4. The range of temperatures for the use of the berms is from -22 $^{\circ}$ F to +158 $^{\circ}$ F.
- 5. The berms are resistant to a large number of different liquids and loose materials (see the Chemical resistance certificate, p. 10). For unknown substances we recommend using the protective insert, which enhances the berm's resistance. The protective insert is an optional accessory.
- 6. The berms are not intended for long-term storage of aggressive substances.
- 7. Fill the berm up only to the upper weld joint of the reinforcement.
- Do not move or pull an empty or a filled berm on the ground the manufacturer's warranty does not cover mechanical damage.
- 9. Use the handling belts (which are also suitable for being hung on the fork of a fork lift truck) to move a filled berm.
- 10. Make sure not to exceed the maximum carrying capacity of 441 lb.
- 11. After each use it is necessary to wash the berm thoroughly, clean it with suitable detergents and let it dry completely.
- 12. Observe the safety measures for working with hazardous liquids and with substances harmful to the environment.
- 13. Make sure you observe any necessary precautions regarding personal safety, such as the use of protective equipment.



Recommended optional accessories

The following optional accessories for collapsible spill berms are provided for a surcharge.

Accessories for Collapsible spill berms ECCOTARP

Туре	ET 01 S	ET 02 M	ET 03 L	ET 04 XL HIGH	ET 041 XL LOW	ET 051 XXL EASY PACK	ET 06 SHALLOW
Pad ET 095-10 (mm)	39 × 20	51 × 51	51 × 51	87 × 87	87 × 87	87 × 87	51 × 51
Protective insert ET 11-16	yes	yes	yes	yes	yes	yes	
Drain hole D25/other		yes	yes	yes	yes	yes	
Ball valve D25/other		yes	yes	yes	yes	yes	
16ft hose with outlet D25		yes	yes	yes	yes	yes	

Accessories for Collapsible spill berms CARGO

Туре	ET 061 CARGO EUR	ET 062 CARGO DP
Protective pad ET 09 (mm)	51 × 51	51 × 51
Drain hole D25/other	yes	yes
Ball valve D25/other	yes	yes
16ft hose with outlet D25	yes	yes

Secure the protective insert in the ready berm using the metal clips. Using the berm with the protective insert increases chemical resistance, makes disposal of collected substance easier and protects the berm, which, as a result, does not need to be cleaned. The collected liquid must be disposed of in compliance with applicable regulations. The protective insert can be cleaned in the same way as the berm and then reused.

The protective pad and the protective insert significantly extend the berm's life.

Maintenance and storage

After the draining and prescribed environment-friendly disposal of the collected substance, the product must be washed with proper neutralization detergent (in the case of aggressive substances) and lukewarm water or another suitable detergent. We recommend storing the berms folded in the carrying bag so that they are not damaged while not in use. The berm must be dried thoroughly before it is put into the bag. For long-term storage, place the berm in a dry place out of the reach of UV radiation.

Important contact information

Qualified service: ECCOTARP USA, inc. 357 West 36th Street New York, NY 10018 USA

info@eccofighter.com T: 1 212-725-9845

Repair

Any repair work on the collapsible berms must always be done by the manufacturer's qualified personnel. In the event of unprofessional repair or design change, the product's proper operation cannot be guaranteed. If you want to request repair, order accessories or lodge a complaint, please, contact your qualified supplier.

Warranty conditions

The warranty period is indicated in the warranty certificate on the last page of these Instructions for use. The warranty period is 24 months and begins on the day indicated in the warranty certificate. The warranty does not apply to the normal wear and tear or to damage caused by improper use or by the instructions in this manual not being observed.

Warning – the warranty does not cover damage from long-term exposure to chemicals. This can also occur after the product is improperly cleaned after intervention. Even a small amount of aggressive chemicals will cause degradation of the material from which it is made during long-term exposure. This can be manifested by microscopic cracks on the surface, or by a change in the properties of the material, which can lead to easy damage and tearing.

Disposal

The berm and/or the used insert must be disposed of in compliance with applicable legal regulations and with the user's internal directives.

Chemical resistance certificate

Applicable to all types of Collapsible Spill Berms, Tanks, Funnels, Drip trays and Protective Liners.

Resistance levels:

A) resistant

- B) resistant for at least 3 hours
- C) non-resistant

Name of substance	Chemical formula	Resistance level at the tem- perature of 68 °C	Resistance level at the tem- perature of 140 °C	Name of substance	Chemical formula	Resistance level at the tem- perature of 68 °C	Resistance level at the tempe- rature of 140 °C
LIQUID SUBSTANCES							
Acetone	CH ₃ COCH ₃	C	C	Hydrogen sulphide	H₂S	A	В
Acetonitrile	CH₃CN	A	A	Styrene	C _s H _s	Α	A
Ammonia	NH3	A	Α	Pentane	C ₆ H ₁₂	A	A
Benzene	C ₆ H ₆	В	В				
Tar	mixture	C	C	Toluene	C ₆ H ₅ CH ₃	C	C
Dimethyl- formamide	C ₃ H ₇ NO	A	A	Salt water Water	H ₂ O	A	A
Ethanol	C ₂ H ₂ OH	В	В	Hvdrogen	H ₂ O	A	A
Ethylene glycol	C,H,O,	В	В	peroxide	H ₂ U ₂	A	А
Ethyl acetate	C ₄ H ₈ O ₂	с	с	Kerosene	C ₉ -C ₁₆	с	с
Ethylbenzene	C ₈ H ₁₀	А	Α				
Formaldehyde	CH ₂ O	В	В	SOLID SUBSTANCES			
Chlorine	CI	С	С	Ammonium	CH₃COONH₄	A	А
Chloroform	CHCl ₃	C	С	Borax	Na ₂ [B ₄ O ₅ (OH) ₄]+8H ₂ O	Α	A
Transformer oil		A	Α	Sugar	mixture	A	A
Gear oil		В	В	Potassium cyanide	KCN	A	A
SAE 40 oil		A	Α	Ammonium nitrate	NH4NO3	A	A
Lubricating oil		A	Α	Calcium nitrate	Ca(NO ₃),	A	A
Silicone oil		Α	Α	Phenol	C ₆ H ₅ OH	B	B
Turpentine dis- tillates		В	В	Ammonium	(NH ₄) ₃ PO ₄	A	A
Hydrochloric acid	HCI	В	В	phosphate	1010	A	A
Nitric acid	HNO ₃	В	В	Potassium nitrate	KNO ₃		A
Phosphoric acid	H₃PO₄	A	В	Potassium	NaOH	A	A
Formic acid	НСООН	В	В	Sodium hydroxide			
Acetic acid	CH ₃ COOH	A	В	Ammonium chloride	NH₄CI	A	A
Sulphuric acid	H_2SO_4	A	В				
Sulphurous acid	H ₂ SO ₃	A	В	OPERATING FLUIDS			
Isopropyl alcohol	C ₃ H ₈ O	В	В	Gas		В	В
Methanol	CH ₃ OH	В	В	Diesel fuel		В	В
Methylene chloride	CH ₂ Cl ₂	С	С	Motor oil		В	В
Sodium chloride solution 20%	NaCl	А	A	Methyl tert-butyl ether (MTBE)	$C_{s}H_{12}O$	В	В
Mercury	Hg	А	A	Hydraulic oils		В	В

Notice:

Eccotarp collapsible products are compatible to varying degrees with the substances listed above.

However, given the almost unlimited number of potential combinations of chemicals plus the influence of factors such as concentration and temperature, this list does not claim to be definitive and is only intended for informative purposes in predicting the behaviour of the chemicals concerned.

Compatibility with the listed substances cannot be entirely guaranteed. Neither the manufacturer nor the distributor provides any warranty, nor do they accept any responsibility for resultant damage.

For a reliable estimate of the level of resistance to a specific substance, we recommend you to test small samples using miniature laboratory funnels which can be provided upon request by the manufacturer. Given that it is not always possible to identify and assess the nature of corrosive substances, the manufacturer recommends using the Eccotarp protective liner.



Eccotarp collapsible products are not intended for long-term storage of retrieved spilt liquids. They were developed first and foremost for rapid use in emergencies, for capturing hazardous substances during the time immediately before its correct disposal.

Notes		

Warranty Certificate



This product is guaranteed for 24 months.

This warranty covers:

for defects caused by a manufacturing defect of the material used, in particular a leak at the welds, a defect in the fittings and any other damage, not caused by demonstrable mishandling by the user or any modification of the product.

This warranty does not cover:

damages caused by improper handling and use of the product and failure to follow the "user manual". For example, punctures or other damage caused by placing the product in an inappropriate area with sharp objects, higher load handling weight than stated in the "user manual", use or placing the product near open flames, and other inappropriate uses.

Warning – the warranty does not cover damage from long-term exposure to chemicals. This can also occur after the product is improperly cleaned after intervention. Even a small amount of aggressive chemicals will cause degradation of the material from which it is made during long-term exposure. This can be manifested by microscopic cracks on the surface, or by a change in the properties of the material, which can lead to easy damage and tearing.

The manufacturer is not liable for direct or indirect damage caused by other than the recommended use of the product.

Complaints must be applied within 24 months of purchase from your supplier. When applying please provide your complaint with full details – product serial number, proof of purchase, appropriate photographic documentation and a detailed description of the circumstances in which a fault has occurred.

Product name:	 		
Production code:	 	Stamp and signature:	
Date of sale:	 	In case of problems, please contac	
Failure description:	 		